

Art.-Nr.: 11.01.41.00092




EVE-TR 25 AC3 IE3-TYP4 VBV

Technical data

Attribute	Value
Rated power at 50 Hz	0.75 kW
Rated power at 60 Hz	0.90 kW
Voltage at 50 Hz	D290 V / Y500 V ± 10 %
Voltage at 60 Hz	D330 V / Y575 V ± 10 %
Weight	27.500 kg
Suction rate (50 Hz)	25.000 m ³ /h
Suction rate (60 Hz)	30.000 m ³ /h
Sound pressure level at 50 Hz	62.0 dB(A)
Version	IE3:CAN
Vacuum (50 Hz)	-600 mbar
Approval	UL/CSA
Category	Electrical vacuum generation

Design data

Attribute	Value
Length L2	96.00 mm
Length L	505.00 mm
Width B2	21.00 mm
Width B	260.00 mm
Height H	290.00 mm
Internal diameter d	7.00 mm
Thread G2	G3/4"-F
Hole spacing X1	220.0 mm
Thread G3	G3/4"-F



Design data EVE-TR 25 AC3 IE3-TYP4 VBV

Art.-Nr.: 11.01.41.00092

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	0.75 kW
Rated power at 60 Hz	0.90 kW
Voltage at 50 Hz	D290 V / Y500 V ± 10 %
Voltage at 60 Hz	D330 V / Y575 V ± 10 %
Weight	27.500 kg
Suction rate (50 Hz)	25.000 m ³ /h
Suction rate (60 Hz)	30.000 m ³ /h
Sound pressure level at 50 Hz	62.0 dB(A)
Version	IE3:CAN
Category	Electrical vacuum generation

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/11.01.41.00092

