




SBL-260-520-IE3-TYP3

Technical data

Attribute	Value
Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.80 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	62.000 kg
Suction rate (50 Hz)	260.000 m ³ /h
Suction rate (60 Hz)	300.000 m ³ /h
Sound pressure level at 50 Hz	74.0 dB(A)
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	-520 mbar
Category	Electrical vacuum generation

Design data

Attribute	Value
Length L	512.00 mm
Width B	473.00 mm
Height H	523.00 mm
Internal diameter d	12.00 mm
Hole spacing X1	310.0 mm



Design data SBL-260-520-IE3-TYP3

Art.-Nr.: 11.02.05.10158

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.80 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	62.000 kg
Suction rate (50 Hz)	260.000 m ³ /h
Suction rate (60 Hz)	300.000 m ³ /h
Sound pressure level at 50 Hz	74.0 dB(A)
Rated power	4.00 W
Version	IE3:JPN/KOR/BRA
Category	Electrical vacuum generation

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/11.02.05.10158