



SBL-260-520-IE3-TYP2

Technical data

Attribute	Value
Rated power at 60 Hz	4.80 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	62.000 kg
Suction rate (50 Hz)	260.000 m ³ /h
Suction rate (60 Hz)	300.000 m ³ /h
Version	IE3:US/CAN
Approval	UL/CSA

Design data

Attribute	Value
Length L	512.00 mm
Width B	473.00 mm
Height H	523.00 mm
Internal diameter d	12.00 mm
Hole spacing X1	310.0 mm

Design data SBL-260-520-IE3-TYP2

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	4.80 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	62.000 kg
Suction rate (50 Hz)	260.000 m ³ /h
Suction rate (60 Hz)	300.000 m ³ /h
Rated power	4.80 W
Version	IE3:US/CAN

Vacuum blower

SBL-260-520-IE3-TYP2



Art.-Nr.: 11.02.05.10183



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/11.02.05.10183



WWW.SCHMALZ.COM/11.02.05.10183