

Suction plate (round)

SPU 300 NBR-55 G1/2-IG



Art.-Nr.: 12.02.04.10433




SPU 300 NBR-55 G1/2-IG

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	300.00
Connection	G1/2"-F

Design data

Attribute	Value
Length L2	76.00 mm
Height H1	26.50 mm
Height H	25.00 mm
d2	253.0 mm
Internal diameter d	34.00 mm
Thread G1	G1/2"-F
Thread length LG1	13.5 mm
Thread G2	G1/2"-F
Thread length LG2	15.0 mm
Hole size d3	226.5 mm
Spring stroke Z	6.0 mm
Diameter Ds	300.0 mm
Diameter Dmax(S)	320.0 mm



Design data SPU 300 NBR-55 G1/2-IG



WWW.SCHMALZ.COM/12.02.04.10433

Suction plate (round)

SPU 300 NBR-55 G1/2-IG



Art.-Nr.: 12.02.04.10433



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	12.0 mm
Suction force (-600mbar)	3,810.00 N
Weight	2,300.00 g
Volume	491.000 cm ³
Size	300.00
Suction force d2	3,010.00 N
Product family	SPU



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/12.02.04.10433



Ordering Data Accessories 12.02.04.10433

Typ		Item number
Protection Covers	PC 300	10.01.01.13091



WWW.SCHMALZ.COM/12.02.04.10433