


Art.-Nr.: 14.05.01.00375



CSKS-SCH-125-5000-SRA105-2614-EL

Technical data

Attribute	Value
Lift capacity	125.0 kg
Overall height	3,130.00 mm
with	Chain hoist



Design data CSKS-SCH-125-5000-SRA105-2614-EL

Design data

Attribute	Value
Length L1	210.00 mm
Length L2	1,040.00 mm
Length L	5,000.00 mm
Height H1	505.00 mm
Height H	3,130.00 mm
Internal diameter d1	20.0 mm
Internal diameter d	15.00 mm
Length L3	210.00 mm
Length L4	515.00 mm
Height H3	31.00 mm

Art.-Nr.: 14.05.01.00375



Technical data

Attribute	Value
Protection type IP	IP 65
Lift capacity	125.0 kg
Weight	188.000 kg
Primary voltage	400V - AC3
Lifting speed (max.)	8 m/min
Lifting speed (min.)	2 m/min
Number of chain strands	1
Frequency	50.0 Hz



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/14.05.01.00375

