



Technical data

Attribute	Value
Weight	7.500 kg
Stroke Z	1,400.00 mm
Drive type	Electrical

RH-BIN-30-NEO30-EL-1400

The rope balancer NEO 30 is supplied as a complete system ready-to-connect. The system consists of:


- Rope balancer NEO 30
- Swivel joint
- Adapter
- Charger
- Two batteries
- Hook with spring lock

Available spare parts: battery, charger, rope, pick-up adapter, socket pin, suspension eye, suspension hook (standard)

Available accessories: scissors clamp, suspension hook (safety hook), suspension hook (canister hook), magnetic gripper



Art.-Nr.: 18.05.08.00015

**Design data**

Attribute	Value
Length L	121.00 mm
Width B	132.00 mm
Height H	410.00 mm
Stroke Z	1,400.00 mm

Design data RH-BIN-30-NEO30-EL-1400

**Technical data**

Attribute	Value
Lift capacity	30.0 kg
Weight	7.500 kg
Drive type	Electrical
Stroke speed (maximum)	0.5 m/sec

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/18.05.08.00015WWW.SCHMALZ.COM/18.05.08.00015

Art.-Nr.: 18.05.08.00015

**Ordering Data Accessories 18.05.08.00015**

Typ		Item number
Scissor clamping gripper	SZ 270-500 NEO30	18.05.08.00024
Single-hook head (inst.)	EH-MON-28-d32x70 NEO30	18.05.08.00023
Single-hook head (inst.)	EH-MON-28-d15x10 NEO30	18.05.08.00028
Magnetic gripper	SGM 27 NEO30	18.05.08.00025

**Ordering Data Spare Parts 18.05.08.00015**

Typ		Item number
Single-hook head (inst.)	EH-MON-30-d33x20 NEO30	18.05.08.00020
Suspension rope balancer	SUS-RH BIN NEO30 30 103x45 20.2	18.05.08.00016
Mounting adapter	ADP-A RA-A1 NEO30	18.05.08.00021
Socket pin	STEC-BOLZ 8x35	18.05.08.00022
Rope	SEIL 3x7000	18.05.08.00017
Battery	BATT-100x180x25-14.4V-DC	18.05.08.00018
Battery charger	LADE-GER-24V-DC-14.4V-DC-1.7	18.05.08.00019

