

Single-hook head (inst.)

# EH-MON-28-d32x70 NEO30



Art.-Nr.: 18.05.08.00023




EH-MON-28-d32x70 NEO30

## Technical data

| Attribute           | Value     |
|---------------------|-----------|
| Length L            | 95.00 mm  |
| Width B1            | 70.00 mm  |
| Width B             | 70.00 mm  |
| Height H            | 236.00 mm |
| Internal diameter d | 32.00 mm  |

## Design data

| Attribute           | Value     |
|---------------------|-----------|
| Utilization design  | Neo 30    |
| Length L            | 95.00 mm  |
| Width B1            | 70.00 mm  |
| Width B             | 70.00 mm  |
| Height H            | 236.00 mm |
| Internal diameter d | 32.00 mm  |



Design data EH-MON-28-d32x70 NEO30



[WWW.SCHMALZ.COM/18.05.08.00023](http://WWW.SCHMALZ.COM/18.05.08.00023)

Single-hook head (inst.)

## EH-MON-28-d32x70 NEO30



Art.-Nr.: 18.05.08.00023



### Technical data

| Attribute           | Value |
|---------------------|-------|
| Clamping range [mm] | mm    |



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/18.05.08.00023](http://www.schmalz.com/18.05.08.00023)



[WWW.SCHMALZ.COM/18.05.08.00023](http://WWW.SCHMALZ.COM/18.05.08.00023)