


Suction cup connection nipple (inst)

SA-NIP N009 G1/4-IG




Art.-Nr.: 10.01.01.10096



Technical data

Attribute	Value
Material	Aluminum
Length L1	33.00 mm
Thread G1	G1/4"-F

SA-NIP N009 G1/4-IG



Design data SA-NIP N009 G1/4-IG

Design data

Attribute	Value
Length L1	33.00 mm
Length L	23.00 mm
Nominal diameter dn	5.50 mm
Thread G1	G1/4"-F
Thread length LG1	12.0 mm
Thread G2	M10x1.25-M
Key width SW1	17.0 mm



Technical data

Attribute	Value
Nipple family	N 009
Weight	12.0 g
Material	Aluminum



WWW.SCHMALZ.COM/10.01.01.10096

Art.-Nr.: 10.01.01.10096



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.10096



Ordering Data Accessories 10.01.01.10096

Typ		Item number
Flat suction cup (round)	PFG 60 FPM-65 N009 M10x1.25-IG	10.01.01.00078
Flat suction cup (round)	PFG 60 HT1-60 N009 M10x1.25-IG	10.01.01.11169
Flat suction cup (round)	PFG 60 NBR-55 N009 M10x1.25-IG	10.01.01.00018
Flat suction cup (round)	PFG 60 PU-55 N009 M10x1.25-IG	10.01.01.00058
Flat suction cup (round)	PFG 60 SI-55 N009 M10x1.25-IG	10.01.01.00038
Flat suction cup (round)	PFG 80 FPM-65 N009 M10x1.25-IG	10.01.01.00079
Flat suction cup (round)	PFG 80 HT1-60 N009 M10x1.25-IG	10.01.01.11170
Flat suction cup (round)	PFG 80 NBR-55 N009 M10x1.25-IG	10.01.01.00019
Flat suction cup (round)	PFG 80 PU-55 N009 M10x1.25-IG	10.01.01.00059
Flat suction cup (round)	PFG 80 SI-55 N009 M10x1.25-IG	10.01.01.00039
Flat suction cup (round)	PFG 95 FPM-65 N009 M10x1.25-IG	10.01.01.00080
Flat suction cup (round)	PFG 95 NBR-55 N009 M10x1.25-IG	10.01.01.00020
Flat suction cup (round)	PFG 95 PU-55 N009 M10x1.25-IG	10.01.01.00060
Flat suction cup (round)	PFG 95 SI-55 N009 M10x1.25-IG	10.01.01.00040