



Art.-Nr.: 10.01.01.03528



SA-NIP N004 G1/8-AG DN200

Technical data

Attribute	Value
Material	Aluminum
Length L1	17.00 mm
Thread G1	G1/8"-M
Fitting length	5.00 mm



Design data SA-NIP N004 G1/8-AG DN200

Design data

Attribute	Value
Length L1	17.00 mm
Length L2	2.00 mm
Length L	5.00 mm
Outside diameter D2	4.0 mm
Outside diameter D	6.00 mm
Nominal diameter dn	2.00 mm
Thread G1	G1/8"-M
Thread length LG1	8.0 mm
Key width SW1	14.0 mm
Length L3	2.00 mm

**Technical data**

Attribute	Value
Nipple family	N 004
Weight	4.0 g
Material	Aluminum



Art.-Nr.: 10.01.01.03528

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.03528**Ordering Data Accessories 10.01.01.03528**

Typ		Item number
Flat suction cup (round)	PFG 10 FPM-65 N004	10.01.01.00070
Flat suction cup (round)	PFG 10 HT1-60 N004	10.01.01.11161
Flat suction cup (round)	PFG 10 NBR-CO-55 N004	10.01.01.10066
Flat suction cup (round)	PFG 10 NBR-55 N004	10.01.01.00010
Flat suction cup (round)	PFG 10 PU-55 N004	10.01.01.00050
Flat suction cup (round)	PFG 10 SI-CO-55 N004	10.01.01.00701
Flat suction cup (round)	PFG 10 SI-55 N004	10.01.01.00030
Flat suction cup (round)	PFG 5 FPM-65 N004	10.01.01.00067
Flat suction cup (round)	PFG 5 HT1-60 N004	10.01.01.11158
Flat suction cup (round)	PFG 5 NBR-CO-55 N004	10.01.01.10064
Flat suction cup (round)	PFG 5 NBR-55 N004	10.01.01.00007
Flat suction cup (round)	PFG 5 SI-CO-55 N004	10.01.01.10051
Flat suction cup (round)	PFG 5 SI-55 N004	10.01.01.00027
Flat suction cup (round)	PFG 6 FPM-65 N004	10.01.01.00068
Flat suction cup (round)	PFG 6 HT1-60 N004	10.01.01.11159
Flat suction cup (round)	PFG 6 NBR-CO-55 N004	10.01.01.10065
Flat suction cup (round)	PFG 6 NBR-55 N004	10.01.01.00008
Flat suction cup (round)	PFG 6 SI-CO-55 N004	10.01.01.00626
Flat suction cup (round)	PFG 6 SI-55 N004	10.01.01.00028
Flat suction cup (round)	PFG 8 FPM-65 N004	10.01.01.00069
Flat suction cup (round)	PFG 8 HT1-60 N004	10.01.01.11160
Flat suction cup (round)	PFG 8 NBR-CO-55 N004	10.01.01.10043
Flat suction cup (round)	PFG 8 NBR-55 N004	10.01.01.00009
Flat suction cup (round)	PFG 8 PU-55 N004	10.01.01.00049
Flat suction cup (round)	PFG 8 SI-CO-55 N004	10.01.01.00647
Flat suction cup (round)	PFG 8 SI-55 N004	10.01.01.00029

