

Düz vantuz (yuvarlak)

## SFF 60 EPDM-45 G1/4-IG



Art.-Nr.: 10.01.01.15574




### Teknik veriler

|                            |              |
|----------------------------|--------------|
| Vantuz malzemesi           | EPDM         |
| Malzeme sertliği [Shore A] | 45,0 Shore A |
| Boyut                      | 60,00        |

SFF 60 EPDM-45 G1/4-IG

Vantuz SFF / SFB1 (elastomer parça + bağlantı nipel) monte edilmiş olarak teslim edilir.

Mevcut yedek parçalar: vantuz SFF / SFB1, bağlantı nipel SC



### Tasarım verileri

|                    |          |
|--------------------|----------|
| Yükseklik H        | 46,50 mm |
| Nominal çap dn     | 4,00 mm  |
| Diş uzunluğu LG1   | 12,0 mm  |
| Anahtar boyutu SW1 | 22,0 mm  |
| Yay stroku Z       | 4,0 mm   |
| Çap Ds             | 60,0 mm  |
| Çap Dmax(S)        | 64,0 mm  |
| Diş G1             | G1/4-IG  |

Tasarım verileri SFF 60 EPDM-45 G1/4-IG



[WWW.SCHMALZ.COM/10.01.01.15574](http://WWW.SCHMALZ.COM/10.01.01.15574)

1

Düz vantuz (yuvarlak)

## SFF 60 EPDM-45 G1/4-IG



Art.-Nr.: 10.01.01.15574



### Teknik veriler

|                            |              |
|----------------------------|--------------|
| Vantuz malzemesi           | EPDM         |
| Malzeme sertliği [Shore A] | 45,0 Shore A |
| Çekme kuvveti              | 90,00 N      |
| Emme kuvveti (-600mbar)    | 90,00 N      |
| Boyut                      | 60,00        |
| Körük Sayısı               | 0,0          |
| Ürün ailesi                | SFF          |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



### Sipariş Verisi Yedek Parça 10.01.01.15574

| Typ                   |                      | Ürün numarası  |
|-----------------------|----------------------|----------------|
| Düz vantuz (yuvarlak) | SFF 60 EPDM-45 SC080 | 10.01.01.15210 |
| Schmalz-Konnektör     | SC 080 G1/4-IG       | 10.01.06.03271 |



[WWW.SCHMALZ.COM/10.01.01.15574](http://WWW.SCHMALZ.COM/10.01.01.15574)