

Bellows suction cups (round)  
**FSGA 22 SI-55 G1/8-IG**



Art.-Nr.: 10.01.06.00070



**Technical data**


Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	22.00
Number of folds	1.5
Connection	G1/8"-F
Vacuum connection	G1/8"-F
Nipple material	Aluminum
Material characteristics	FDA-compatible

FSGA 22 SI-55 G1/8-IG

Suction cup FSGA (elastomer part + connection nipple) is delivered unassembled (diameters of 33 mm and more are assembled). The delivery consists of:

- Suction cup of type FGA – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FGA, connection nipple SA-NIP



**Design data**

Height H	31.00 mm
Nominal diameter dn	3.50 mm
d2	11.7 mm
Thread G1	G1/8"-F
Thread length LG1	8.0 mm
Key width SW1	14.0 mm
Spring stroke Z	6.0 mm
Diameter Ds	21.5 mm
Diameter Dmax(S)	25.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FSGA 22 SI-55 G1/8-IG



[WWW.SCHMALZ.COM/10.01.06.00070](http://WWW.SCHMALZ.COM/10.01.06.00070)

# Bellows suction cups (round)

## FSGA 22 SI-55 G1/8-IG



Art.-Nr.: 10.01.06.00070



### Technical data

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	25.0 mm
Pull-off force	15.20 N
Suction force (-600mbar)	5.70 N
Weight	6.20 g
Volume	1.400 cm <sup>3</sup>
Size	22.00
Number of folds	1.5
Product family	FSGA
Connection	G1/8-IG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m



### Ordering Data Accessories 10.01.06.00070

Typ	Item number
Schmalz Pad Insert PEEK   SPI 21 PEEK	10.01.06.03285



### Ordering Data Spare Parts 10.01.06.00070

Typ	Item number
Suction cup connection nipple   SA-NIP N016 G1/8-IG DN350	10.01.06.05731



### Ordering Data Wear Parts 10.01.06.00070

Typ	Item number
Bellows suction cup (round)   FGA 22 SI-55 N016	10.01.06.00100



[WWW.SCHMALZ.COM/10.01.06.00070](http://WWW.SCHMALZ.COM/10.01.06.00070)