

Bellows suction cups (round)

FSG 14 NBR-55 G1/8-IG



Art.-Nr.: 10.01.06.00003



Technical data


Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	14.00
Number of folds	2.5
Connection	G1/8"-F
Vacuum connection	G1/8"-F
Nipple material	Aluminum

FSG 14 NBR-55 G1/8-IG

Suction cup FSG (elastomer part + connection nipple) is delivered unassembled (assembled from a diameter of 32 mm). The delivery consists of:

- Suction cup of type FG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FG, connection nipple SA-NIP



Design data

Attribute	Value
Height H	34.80 mm
Nominal diameter dn	3.50 mm
d2	5.4 mm
Thread G1	G1/8"-F
Thread length LG1	8.5 mm
Key width SW1	14.0 mm
Spring stroke Z	9.0 mm
Diameter Ds	14.5 mm
Diameter Dmax(S)	15.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FSG 14 NBR-55 G1/8-IG



WWW.SCHMALZ.COM/10.01.06.00003

Bellows suction cups (round)
FSG 14 NBR-55 G1/8-IG



Art.-Nr.: 10.01.06.00003



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	15.0 mm
Pull-off force	5.70 N
Suction force (-600mbar)	1.37 N
Weight	5.70 g
Volume	0.975 cm ³
Size	14.00
Number of folds	2.5
Product family	FSG
Connection	G1/8-IG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00003



Ordering Data Accessories 10.01.06.00003

Typ	Item number
Schmalz Pad Insert PEEK	SPI 14 PEEK
	10.01.06.03282



Ordering Data Spare Parts 10.01.06.00003

Typ	Item number
Suction Cup Connection Nipples	SA-NIP N016 G1/8-IG DN350
	10.01.06.05731



Ordering Data Wear Parts 10.01.06.00003

Typ	Item number
Bellows suction cup (round)	FG 14 NBR-55 N016
	10.01.06.00052



WWW.SCHMALZ.COM/10.01.06.00003