

Bellows suction cups (round)

FSG 25 NBR-55 G1/8-AG



Art.-Nr.: 10.01.06.00334



FSG 25 NBR-55 G1/8-AG


Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	25.00
Number of folds	2.5
Connection	G1/8"-M
Vacuum connection	G1/8"-M
Nipple material	Aluminum

Suction cup FSG (elastomer part + connection nipple) is delivered unassembled. The delivery consists of:

- Suction cup of type FG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FG, connection nipple SA-NIP



Design data FSG 25 NBR-55 G1/8-AG

Design data

Attribute	Value
Height H	40.00 mm
Nominal diameter dn	3.50 mm
d2	10.0 mm
Thread G1	G1/8"-M
Thread length LG1	7.5 mm
Key width SW1	14.0 mm
Spring stroke Z	18.0 mm
Diameter Ds	23.0 mm
Diameter Dmax(S)	26.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



Bellows suction cups (round)

FSG 25 NBR-55 G1/8-AG



Art.-Nr.: 10.01.06.00334



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	30.0 mm
Pull-off force	19.00 N
Suction force (-600mbar)	4.71 N
Weight	8.0 g
Volume	5.400 cm ³
Size	25.00
Number of folds	2.5
Product family	FSG
Connection	G1/8-AG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00334



Ordering Data Accessories 10.01.06.00334

Typ		Item number
Sealing ring	DR 22.5/13x2 MOS SI-15	10.01.06.02614
Filter disc	FD 18 120	10.01.06.02567
Schmalz Pad Insert PEEK	SPI 25 PEEK	10.01.06.03286



Ordering Data Spare Parts 10.01.06.00334

Typ		Item number
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN350	10.01.06.05735



Ordering Data Wear Parts 10.01.06.00334

Typ		Item number
Bellows suction cup (round)	FG 25 NBR-55 N016	10.01.06.00335



WWW.SCHMALZ.COM/10.01.06.00334