

Bellows suction cups (round)

FSG 12 NBR-55 M5-AG



Art.-Nr.: 10.01.06.00565



FSG 12 NBR-55 M5-AG


Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Size	12.00
Number of folds	2.5
Connection	M5-M
Vacuum connection	M5-M
Nipple material	Aluminum

Suction cup FSG (elastomer part + connection nipple) is delivered unassembled (assembled from a diameter of 32 mm). The delivery consists of:

- Suction cup of type FG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FG, connection nipple SA-NIP



Design data FSG 12 NBR-55 M5-AG

Design data

Attribute	Value
Height H	26.00 mm
Nominal diameter dn	2.50 mm
d2	5.0 mm
Thread G1	M5-M
Thread length LG1	5.0 mm
Key width SW1	7.0 mm
Spring stroke Z	7.0 mm
Diameter Ds	12.0 mm
Diameter Dmax(S)	13.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



Bellows suction cups (round)

FSG 12 NBR-55 M5-AG



Art.-Nr.: 10.01.06.00565



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	12.5 mm
Pull-off force	3.50 N
Suction force (-600mbar)	1.18 N
Weight	2.20 g
Volume	0.600 cm ³
Size	12.00
Number of folds	2.5
Product family	FSG
Connection	M5-AG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.00565



Ordering Data Accessories 10.01.06.00565

Typ	Item number
Schmalz Pad Insert PEEK	SPI 14 PEEK
	10.01.06.03282



Ordering Data Spare Parts 10.01.06.00565

Typ	Item number
Suction Cup Connection Nipples	SA-NIP N016 M5-AG DN250
	10.01.06.00123



Ordering Data Wear Parts 10.01.06.00565

Typ	Item number
Bellows suction cup (round)	FG 12 NBR-55 N016
	10.01.06.00557



WWW.SCHMALZ.COM/10.01.06.00565