

Bellows suction cups (round)

FSGA 6 SI-55 M5-AG



Art.-Nr.: 10.01.06.02995



FSGA 6 SI-55 M5-AG


Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	6.00
Number of folds	1.5
Connection	M5-M
Vacuum connection	M5-M
Nipple material	Aluminum
Material characteristics	FDA-compatible

Suction cup FSGA (elastomer part + connection nipple) is delivered unassembled (diameters of 33 mm and more are assembled). The delivery consists of:

- Suction cup of type FGA – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FGA, connection nipple SA-NIP



Design data FSGA 6 SI-55 M5-AG

Design data

Attribute	Value
Height H	14.00 mm
Nominal diameter dn	2.00 mm
d2	3.0 mm
Thread G1	M5-M
Thread length LG1	4.5 mm
Key width SW1	8.0 mm
Spring stroke Z	2.0 mm
Diameter Ds	5.7 mm
Diameter Dmax(S)	8.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.06.02995

Bellows suction cups (round)
FSGA 6 SI-55 M5-AG



Art.-Nr.: 10.01.06.02995



Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	4.0 mm
Pull-off force	1.40 N
Suction force (-600mbar)	0.40 N
Weight	1.5 g
Volume	0.151 cm ³
Size	6.00
Number of folds	1.5
Product family	FSGA
Connection	M5-AG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.02995



Ordering Data Spare Parts 10.01.06.02995

Typ		Item number
Suction cup connection nipple	SA-NIP N004 M5-AG DN200	10.01.01.03526



Ordering Data Wear Parts 10.01.06.02995

Typ		Item number
Bellows suction cup (round)	FGA 6 SI-55 N004	10.01.06.01571



WWW.SCHMALZ.COM/10.01.06.02995