

Art.-Nr.: 10.01.06.03074



FSG 4 NBR-CO-55 M5-IG


Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55.0 Shore A
Size	4.00
Number of folds	2.5
Connection	M5-F
Vacuum connection	M5-F
Nipple material	Aluminum

Suction cup FSG (elastomer part + connection nipple) is delivered unassembled (assembled from a diameter of 32 mm). The delivery consists of:

- Suction cup of type FG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FG, connection nipple SA-NIP



Design data FSG 4 NBR-CO-55 M5-IG

Design data

Attribute	Value
Height H	24.00 mm
Nominal diameter dn	2.00 mm
d2	2.4 mm
Thread G1	M5-F
Thread length LG1	5.5 mm
Key width SW1	8.0 mm
Spring stroke Z	1.5 mm
Diameter Ds	3.8 mm
Diameter Dmax(S)	5.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Bellows suction cups (round)

FSG 4 NBR-CO-55 M5-IG



Art.-Nr.: 10.01.06.03074



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	4.0 mm
Pull-off force	0.60 N
Suction force (-600mbar)	0.27 N
Weight	1.80 g
Volume	0.053 cm ³
Size	4.00
Number of folds	2.5
Product family	FSG
Connection	M5-IG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03074



Ordering Data Spare Parts 10.01.06.03074

Typ	Item number
Suction cup connection nipple	SA-NIP N017 M5-IG DN200 10.01.06.00313



Ordering Data Wear Parts 10.01.06.03074

Typ	Item number
Bellows suction cup (round)	FG 4 NBR-CO-55 N017 10.01.06.03067



WWW.SCHMALZ.COM/10.01.06.03074