

Bellows suction cups (round)

SPB2f 40 SI-55 G1/4-AG



Art.-Nr.: 10.01.06.03648



SPB2f 40 SI-55 G1/4-AG

Suction cup SPB2f (elastomer part + connection element) is delivered assembled. The assembly consists of:

- Suction cup of type SPB2f - elastomer part, available in various diameters
- Connection element of type SC - available with various threads


Available spare parts: suction cup SPB2f, Schmalz-Connector

Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	40.00
Number of folds	2.5
Thread G1	G1/4"-M

Design data

Attribute	Value
Height H	44.50 mm
Nominal diameter dn	8.00 mm
d2	15.3 mm
Thread G1	G1/4"-M
Thread length LG1	10.0 mm
Key width SW1	22.0 mm
Spring stroke Z	7.0 mm
Diameter Ds	39.7 mm
Diameter Dmax(S)	42.0 mm



Design data SPB2f 40 SI-55 G1/4-AG



WWW.SCHMALZ.COM/10.01.06.03648

Bellows suction cups (round)
SPB2f 40 SI-55 G1/4-AG



Art.-Nr.: 10.01.06.03648



Technical data

Attribute	Value
Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	9.0 mm
Suction force (-600mbar)	20.40 N
Weight	23.2 g
Volume	12.887 cm ³
Size	40.00
Number of folds	2.5
Suction force at -400 mbar	13.60 N
Suction force at -200 mbar	6.80 N
Product family	SPB2f

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.03648



Ordering Data Accessories 10.01.06.03648

Typ	Item number
Hose clamp	SSB 16-27 ST-VZ 10.07.10.00002



Ordering Data Spare Parts 10.01.06.03648

Typ	Item number
Schmalz-Connector	SC 080 G1/4-AG 10.01.06.03268



Ordering Data Wear Parts 10.01.06.03648

Typ	Item number
Bellows suction cup (round)	SPB2f 40 SI-55 SC080 10.01.06.03559



WWW.SCHMALZ.COM/10.01.06.03648