


Art.-Nr.: 10.01.06.04158



Technical data


Attribute	Value
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Size	9.00
Number of folds	2.5
Connection	G1/8"-M
Vacuum connection	G1/8"-M
Nipple material	Aluminum
Material characteristics	FDA-compatible

FSG 9 SI-HD-65 G1/8-AG

Suction cup FSG (elastomer part + connection nipple) is delivered unassembled. The delivery consists of:

- Suction cup of type FG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FG, connection nipple SA-NIP



Design data

Attribute	Value
Height H	21.00 mm
Nominal diameter dn	3.50 mm
d2	4.1 mm
Thread G1	G1/8"-M
Thread length LG1	7.5 mm
Key width SW1	14.0 mm
Spring stroke Z	3.0 mm
Diameter Ds	9.0 mm
Diameter Dmax(S)	9.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FSG 9 SI-HD-65 G1/8-AG



Art.-Nr.: 10.01.06.04158

**Technical data**

Attribute	Value
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	10.0 mm
Pull-off force	2.30 N
Suction force (-600mbar)	0.79 N
Weight	4.5 g
Volume	0.150 cm ³
Size	9.00
Number of folds	2.5
Product family	FSG
Connection	G1/8-AG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.06.04158

**Ordering Data Spare Parts 10.01.06.04158**

Typ	Item number
Suction cup connection nipple	SA-NIP N016 G1/8-AG DN350 10.01.06.05735

**Ordering Data Wear Parts 10.01.06.04158**

Typ	Item number
Bellows suction cup SI-HD (round)	FG 9 SI-HD-65 N016 10.01.06.03148

