

Art.-Nr.: 10.01.06.04209



## Technical data


Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Size	25.00
Number of folds	1.5
Connection	G1/8"-F
Vacuum connection	G1/8"-F
Nipple material	Aluminum
Material characteristics	FDA-compatible

FSGA 25 SI-MD-55 G1/8-IG

Suction cup FSGA (elastomer part + connection nipple) is delivered unassembled (diameters of 33 mm and more are assembled). The delivery consists of:

- Suction cup of type FGA – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup FGA, connection nipple SA-NIP



## Design data

Height H	35.00 mm
Nominal diameter dn	3.50 mm
d2	9.9 mm
Thread G1	G1/8"-F
Thread length LG1	8.0 mm
Key width SW1	14.0 mm
Spring stroke Z	9.0 mm
Diameter Ds	22.5 mm
Diameter Dmax(S)	26.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data FSGA 25 SI-MD-55 G1/8-IG



Art.-Nr.: 10.01.06.04209

**Technical data**

Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Pull-off force	17.30 N
Suction force (-600mbar)	5.30 N
Weight	6.80 g
Volume	3.150 cm <sup>3</sup>
Size	25.00
Number of folds	1.5
Product family	FSGA
Connection	G1/8-IG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.06.04209**

Typ	Item number
Schmalz Pad Insert PEEK   SPI 25 PEEK	10.01.06.03286

**Ordering Data Spare Parts 10.01.06.04209**

Typ	Item number
Suction cup connection nipple   SA-NIP N016 G1/8-IG DN350	10.01.06.05731

**Ordering Data Wear Parts 10.01.06.04209**

Typ	Item number
Bellows suction cup SI-MD (round)   FGA 25 SI-MD-55 N016	10.01.06.04153

