

### Technical data


| Attribute             | Value              |
|-----------------------|--------------------|
| Length L              | 145.00 mm          |
| Width B               | 130.00 mm          |
| Height H              | 26.00 mm           |
| for                   | Flat table systems |
| Working height H (AH) | 100.00 mm          |

AP-G-145x130x26

The adapter plate AP-G is delivered assembled. The product consists of:

- Main body made of aluminum
- Friction plate bottom

Available accessories: vacuum block, push-in fitting union, screw plug with collar, push-in nipple, compressed air coupling



### Design data

| Attribute | Value     |
|-----------|-----------|
| Length L  | 145.00 mm |
| Width B   | 130.00 mm |
| Height H  | 26.00 mm  |

Design data AP-G-145x130x26



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.12.03876](http://www.schmalz.com/10.01.12.03876)


[WWW.SCHMALZ.COM/10.01.12.03876](http://WWW.SCHMALZ.COM/10.01.12.03876)

Art.-Nr.: 10.01.12.03876

**Ordering Data Accessories 10.01.12.03876**

| Typ                       |                             | Artikelnummer  |
|---------------------------|-----------------------------|----------------|
| Vacuum block              | VCBL-B 140x130x29 TV        | 10.01.12.03165 |
| Vacuum block              | VCBL-B 140x130x48 TV        | 10.01.12.03169 |
| Vacuum block              | VCBL-B 140x130x74 TV        | 10.01.12.03173 |
| Vacuum block              | VCBL-B 125x75x29 TV         | 10.01.12.03166 |
| Vacuum block              | VCBL-B 125x75x48 TV         | 10.01.12.03170 |
| Vacuum block              | VCBL-B 125x75x74 TV         | 10.01.12.03174 |
| Vacuum block              | VCBL-B 120x50x29 TV         | 10.01.12.03167 |
| Vacuum block              | VCBL-B 120x50x48 TV         | 10.01.12.03171 |
| Vacuum block              | VCBL-B 120x50x74 TV         | 10.01.12.03175 |
| Vacuum block              | VCBL-B 130x30x29 TV         | 10.01.12.03168 |
| Vacuum block              | VCBL-B 130x30x48 TV         | 10.01.12.03172 |
| Vacuum block              | VCBL-B 130x30x74 TV         | 10.01.12.03176 |
| Plug union, elbow         | STV-W G1/4-AG 4             | 10.08.02.00157 |
| Plug union, elbow         | STV-W G1/4-AG 6             | 10.08.02.00159 |
| Plug union, elbow         | STV-W G1/4-AG 8             | 10.08.02.00161 |
| Plug union, elbow         | STV-W G1/4-AG 10            | 10.08.02.00254 |
| Plug union, elbow         | STV-W G1/4-AG 12            | 10.08.02.00162 |
| Sealing screw with collar | VRS-SB G1/4-AG ISKT O-Ring  | 10.08.06.00044 |
| Plug-in nipple            | EINS-NIP G1/4-IG 7.2 MS     | 10.01.12.04712 |
| Pneumatic coupling        | DRUC-KUPP D27 G1/4-AG NW7.2 | 10.01.12.04713 |

