



## Technical data


Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Additional function suction cup	Friction disc
Connection	G3/8-AG
Nipple material	Aluminum

## SAOXM 80x30 ED-85 G3/8-AG

Bell-shaped suction cup SAOXM (elastomer part with insert including friction disc + connection element) is delivered assembled. The assembly consists of:

- Bell-shaped suction cup of type SAOXM – elastomer part, available in various dimensions
- Insert – including moulded friction disc
- Connector upper part – available with various threads
- Connector lower part

Available spare parts: suction cup SAOXM, Schmalz-Connector-Insert, Schmalz-Connector upper part (Schmalz-Connector-Adapter), Schmalz-Connector lower part (Schmalz-Connector-Screw)



## Design data

Height H	30.30 mm
Nominal diameter dn	4.10 mm
Thread G1	G3/8"-M
Thread length LG1	8.0 mm
Key width SW1	19.0 mm
Spanner size SW2	4.0 mm
Spring stroke Z	6.0 mm
Suction cup width Bs	31.90 mm
Ls	82.10 mm
Key width SW3	5.0 mm
Lmax.(S)	88.00 mm
Bmax(S)	41.50 mm

## Design data SAOXM 80x30 ED-85 G3/8-AG



Art.-Nr.: 10.01.24.00037

**Technical data**

Suction cup material	Elastodur ED
Material hardness [Shore A]	85.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Suction force (-600mbar)	105.00 N
Weight	37.40 g
Dimension (LxW)	80 x 30
Lateral force	110.0 N
Lateral force oily surface	134.0 N
Volume	13.000 cm <sup>3</sup>
Product family	SAOXM

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Spare Parts 10.01.24.00037**

Typ		Item number
Bell suction cup (oval)	SAOXM 80x30 ED-85 SC045-AR	10.01.24.00002
Schmalz-Connector-Insert	SC-I 045 AR-FDC	10.01.24.00010
Schmalz-Connector-Adapter	SC-A 045-AR G3/8-AG L	10.01.06.03133
Schmalz-Connector-Screw	SC-S 045 L	10.01.06.02740

**Ordering Data Wear Parts 10.01.24.00037**

Typ		Item number
Bell suction cup (oval)	SAOXM 80x30 ED-85 SC045-AR	10.01.24.00002
Schmalz-Connector-Insert	SC-I 045 AR-FDC	10.01.24.00010

