

Art.-Nr.: 10.01.27.01752



MPL 400x300x28 12,5x12,5 3x3

Technical data


Attribute	Value
Slot	3 x 3 mm mm
Length L	400.00 mm
Width B	300.00 mm
Grid	12,5x12,5

The Matrix-Plate MPL from Schmalz is delivered pre-assembled. The delivery consists of:

- Matrix-Plate made of aluminum incl. grid groove, vacuum distribution and optional friction pads
- Sealing cord, mechanical stops and screw fittings
- Vacuum connection set incl. manual slide valve for hoses with inner diameter 12 mm and 25 mm
- Vacuum gauge

Available spare parts: Mechanical stops, friction pads, sealing cord

Available accessories: Connecting elements, vacuum connection set, vacuum gauge, Steel-Plate ISST-MPL for ISBL, Steel-Plate ISST-MPL SFM for SFM



Design data MPL 400x300x28 12,5x12,5 3x3

Design data

Attribute	Value
Length L2	12.50 mm
Length L	400.00 mm
Width B2	12.50 mm
Width B	300.00 mm
Height H2	3.00 mm
Height H	28.00 mm
Length L3	3.00 mm
Length L4	200.00 mm
Width B3	3.00 mm
Width B4	200.00 mm



Art.-Nr.: 10.01.27.01752

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.27.01752**Ordering Data Accessories 10.01.27.01752**

Typ		Artikelnummer
Hollow screw with collar	SCHR G1/4x31 6.00	10.01.27.00163
Steel-Plate	ISST-MPL 400x300x3	10.01.28.00019
Steel-Plate	ISST-MPL 400x300x3 SFM	10.01.28.00022
Schmalz FlexMat	SFM-298.5x198.5	10.01.28.00005
Vacuum block Innospann	ISBL-HD 80x80x38	10.01.15.00654
Vacuum block Innospann	ISBL-HD 80x40x38	10.01.15.00655
Vacuum block Innospann	ISBL-HD 80x28x38	10.01.15.00656

**Ordering Data Spare Parts 10.01.27.01752**

Typ		Artikelnummer
Connection set	SET VC-MPL G1/2-IG	10.01.27.01732
Connection set	SET VC-MPL 4/2	10.01.27.01733
Stop matrixplate	ANSG-MPL 8x15x30	10.01.27.00079
Sieve with male thread	SIEB G1/8x3.5 MS 0.27/0.15 ISKT	10.05.03.00008
Sealing screw with collar	VRS-SB G1/8-AG ISKT Di-Ring	10.08.06.00059
Sealing cord	DI-SCHN 3.5 MOS CR-20	10.07.04.00091
Sealing cord	DI-SCHN 3 MOS CR-20	10.07.04.00088
Vacuum gauge	VAM 40 V U BAR	10.07.02.00046
Manuel slide valve	HSV 12 3/2 G1/2-IG	10.05.07.00036
Vacuum hose (meter)	VSL 4-2 PU MI-TR	10.07.09.00001
Vacuum hose (meter)	VSL 10-7 PU MI-TR	10.07.09.00084
Compressed-air hose	VSL 21-12 PVC-G KL-TR	10.07.09.00006
Vacuum hose (meter)	VSL 33-25 PVC-DS KL-TR	10.07.09.00041
Hose sleeve	ST G1/2-AG 13 MS-V	10.08.03.00162
Hose sleeve	ST G3/4-AG 25 MS-V	10.08.03.00223
Plug union, elbow	STV-W G1/4-AG 10	10.08.02.00254
Plug union, straight	STV-GE G1/4-AG 10	10.08.02.00251

