



VAGG 63 AC3 80 MD


The vacuum unit VAGG is supplied as a product ready to connect.

Available spare parts: vacuum gauge, oil, spare parts set float, wear parts set vacuum pump, vacuum pump

Available accessories: vacuum hose

### Technical data

| Attribute           | Value                    |
|---------------------|--------------------------|
| Suction rate (max.) | 63.000 m <sup>3</sup> /h |
| Reservoir volume    | 80.0 l                   |



Design data VAGG 63 AC3 80 MD

### Design data

| Attribute           | Value     |
|---------------------|-----------|
| Length L            | 994.00 mm |
| Width B             | 435.00 mm |
| Height H            | 926.00 mm |
| Outside diameter D1 | 14.0 mm   |
| Outside diameter D2 | 7.2 mm    |
| Outside diameter D  | 25.00 mm  |

Art.-Nr.: 10.01.27.01972

**Technical data**

| Attribute           | Value            |
|---------------------|------------------|
| Max. vacuum         | 930 mbar         |
| Suction rate (max.) | 63.000 m³/h      |
| Function            | manual drain     |
| Current type        | Three phase A.C. |

**Further documentation**CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.27.01972](http://www.schmalz.com/10.01.27.01972)**Ordering Data Accessories 10.01.27.01972**

| Typ                | Artikelnummer                           |
|--------------------|-----------------------------------------|
| Vacuum distributor | VTR-ZF 8x 1TN MAN/KVZ<br>10.01.27.00126 |

**Ordering Data Spare Parts 10.01.27.01972**

| Typ                               | Artikelnummer                               |
|-----------------------------------|---------------------------------------------|
| Spare part                        | ERS VAGG 6-63<br>10.01.27.01456             |
| Vacuum pump                       | EVE-OG 63 AC3<br>10.03.02.00073             |
| Set of parts subject to wear pump | VST EVE-OG-63-100<br>10.03.02.00055         |
| Oil                               | OEL EVE-OG 1L ANDEROL 555<br>27.02.01.00055 |
| Oil filter                        | OEL-FILT EVE-OG-40-100G<br>10.03.02.00009   |
| Sieve insert                      | SIEB-EINS 24x 41 NLS<br>10.01.27.01862      |
| Pipe (machined)                   | ROHR 40x3x90 VC-SYS<br>10.01.27.00471       |
| Horn                              | HUPE 42.5x43.5 S017 SW<br>21.05.05.00059    |
| Accessories                       | ZUB BEL EVE-OG 63/100-AC3<br>22.09.03.00024 |

