

Art.-Nr.: 10.01.44.00371



FQE Xc 120x60 SW80 SPB2


The area gripper FQE Xc is delivered as a ready-to-connect product. Customized grippers are available on request.

Available spare parts: connection cable, vacuum gauge, vacuum switch, vacuum hose, ejector module, flow restrictor, suction cup

Available accessories: connection cable, vacuum hose, vacuum gauge, vacuum/pressure switch, flexolink, ball joints, vacuum filter

Technical data

Attribute	Value
Nozzle diameter	0.8 mm
Suction cup type	SPB2
Weight	0.330 kg
Design vacuum generator	Ejector module SEP
Number of suction cells	10
Function	controlled
Length L	120.00 mm
Width B	60.00 mm
Height H	70.20 mm
Number of ejectors	2



Design data FQE Xc 120x60 SW80 SPB2

Design data

Attribute	Value
Length L	120.00 mm
Width B	60.00 mm
Height H1	116.00 mm
Height H2	24.30 mm
Height H	70.20 mm
Nominal diameter dn	6.00 mm
Thread G1	G1/8"-F
Thread G2	M5-F
Diameter Ds	20.0 mm
Hole spacing Y1	44.4 mm

Art.-Nr.: 10.01.44.00371

**Technical data**

Attribute	Value
Nozzle diameter	0.8 mm
Suction cup type	SPB2
Construction vacuum switch	PNP switching
Weight	0.330 kg
Air consumption [l/min]	42.0 l/min
Control valve	Normally open

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.44.00371**Ordering Data Accessories 10.01.44.00371**

Typ		Item number
Connection cable	ASK WB-M12-5 5000 K-4P	21.04.05.00557
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002
Vacuum hose (meter)	VSL 8-6 PU MI-TR	10.07.09.00003
Vacuum hose (meter)	VSL 10-7 PE MI-TR	10.07.09.00083
Vacuum hose (meter)	VSL 12-9 PU MI-TR	10.07.09.00037
Vacuum hose (meter)	VSL 14-11 PU MI-TR	10.07.09.00038
Vacuum hose (meter)	VSL 26-19 PVC-DS KL-TR	10.07.09.00007
Vacuum gauge	VAM 40 V U BAR	10.07.02.00046
Vacuum/pressure switch	VSi V D M8-4	10.06.02.00577
Ball joint	KGL G1/8-IG G1/8-AG A2	10.01.03.00109
Vacuum filter (inline)	VFI 6/4 50	10.07.01.00328

**Ordering Data Spare Parts 10.01.44.00371**

Typ		Item number
Connection cable	ASK B-M12-5 5000 K-5P	21.04.05.00080
Connection cable	ASK WB-M12-5 5000 K-4P	21.04.05.00557
Vacuum gauge	VAM 40 V U BAR	10.07.02.00046
Vacuum/pressure switch	VSi V D M8-4	10.06.02.00577
Ejector module	SEP HF 2 06 13	10.02.01.01343
Bellows suction cup (round)	SPB2 20 SI-40 P	10.01.06.03125
Flow resistance	SW 80 P 7.3	10.05.04.00090
Vacuum hose (meter)	VSL 6-4 PTFE MI-TR	10.07.09.00157

