

Mounting profile (machined)

# MO-PROF 25x30x500 1TN AL



Art.-Nr.: 10.01.49.00088




MO-PROF 25x30x500 1TN AL

## Technical data

| Attribute | Value         |
|-----------|---------------|
| Length L  | 500.00 mm     |
| Width B   | 25.00 mm      |
| Height H  | 30.00 mm      |
| Form      | with 1 T-slot |

## Design data

| Attribute | Value     |
|-----------|-----------|
| Length L  | 500.00 mm |
| Width B   | 25.00 mm  |
| Height H  | 30.00 mm  |



Design data MO-PROF 25x30x500 1TN AL



## Technical data

| Attribute | Value         |
|-----------|---------------|
| Material  | Aluminum      |
| Form      | with 1 T-slot |



[WWW.SCHMALZ.COM/10.01.49.00088](http://WWW.SCHMALZ.COM/10.01.49.00088)

Mounting profile (machined)

## MO-PROF 25x30x500 1TN AL



Art.-Nr.: 10.01.49.00088



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.49.00088](http://www.schmalz.com/10.01.49.00088)



### Ordering Data Accessories 10.01.49.00088

| Typ                           |                        | Artikelnummer  |
|-------------------------------|------------------------|----------------|
| Tubing deburrer               | ROHR-ENTGR VEE         | 10.01.36.00043 |
| Tubing deburrer               | ROHR-ENTGR PXT         | 10.01.49.00079 |
| Holder profile tooling        | HP-HT 2M8 56 HT-A3     | 10.07.06.00733 |
| Holder profile for sensor     | HP-SE-U 1M6 12/18      | 10.07.06.00719 |
| Holder profile spring plunger | HP-FST 2M6 35 M18x1.5  | 10.07.06.00722 |
| Holder profile spring plunger | HP-FST 2M6 35 M20x1.5  | 10.07.06.00723 |
| Holder profile suction Cup    | HP-SG 2M6 E 35 G1/4-AG | 10.07.06.00712 |
| Holder profile suction Cup    | HP-SG 2M6 E 35 G3/8-AG | 10.07.06.00715 |
| Holder profile suction Cup    | HP-SG 2M6 E 35 G1/4-IG | 10.07.06.00716 |
| Holder profile suction Cup    | HP-SG 2M6 E 35 G3/8-IG | 10.07.06.00717 |



[WWW.SCHMALZ.COM/10.01.49.00088](http://WWW.SCHMALZ.COM/10.01.49.00088)