

Art.-Nr.: 10.02.02.06591



SCTSi PNT 4


The SCTSi Ethernet compact terminal is supplied as a ready-to-connect product (without connection cable).

Available spare parts: Ejector wearing parts kit

Available accessories: Connection cable

Technical data

Attribute	Value
Communication	Profinet
Number of ejectors	4
Ejector type 1	SCPSt 15 G02 NC
Product key	SCTSi-PNT-4-AB-4C7N-00



Design data SCTSi PNT 4

Design data

Attribute	Value
Length L1	160.20 mm
Length L2	27.00 mm
Length L	126.20 mm
Width B1	124.70 mm
Width B2	13.50 mm
Width B	97.30 mm
Height H2	88.50 mm
Height H	105.00 mm
Internal diameter d	6.00 mm
Thread G1	G1/8"-F



Art.-Nr.: 10.02.02.06591




Technical data


Attribute	Value
Weight	1.120 kg
Communication	Profinet




Performance data



Evacuation time for various vacuum ranges [s/l]



Achievable vacuum at various operating pressures



Suction rate at various degrees of evacuation [l/min]



Art.-Nr.: 10.02.02.06591



Evacuation time for various vacuum ranges [s/l]

Typ	0	100	200	300	400	500	600	700	800
1.5 mm	-	0.07	0.15	0.25	0.4	0.6	0.9	1.3	2.3
2-1.4 mm	-	-	-	0.1	0.2	0.35	0.65	1.2	2.3



Achievable vacuum at various operating pressures

Typ	2	3	4	5	6
1.5 mm	450	660	870	880	865
2-1.4 mm	390	590	800	890	880



Suction rate at various degrees of evacuation [l/min]

Typ	0	100	200	300	400	500	600	700	800
1.5 mm	65.5	57.1	47.4	39.3	32	25.3	17	8.8	1.5
2-1.4 mm	71.8	61.4	52.5	42.2	31.9	23.5	15.3	8.5	1.2



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.02.06591



Ordering Data Accessories 10.02.02.06591

Typ		Item number
Vacuum filter (inline)	VFI CN8/6 50	10.07.01.00245
Vacuum cup filter	VFT G1/8-IG 80	10.07.01.00116
Mounting set	SET SCPS	10.02.02.04343
Exhaust air set	ABL-SET SCPSSt einstufig	10.02.02.05661
Top-hat rail clamp comp.	HUT-SN-KL 75x18x9 SCPS	10.02.02.04149
Power cable	P-LEIT-LK S-M12-5 1.5m B-M12-5	21.04.05.00606
Power cable	P-LEIT-LK S-M12-5 3m B-M12-5	21.04.05.00607
Power cable	P-LEIT-LK B-M12-5 1.5m OK	21.04.05.00351
Power cable	P-LEIT-LK B-M12-5 5m OK	21.04.05.00352
Connection cable	ASK S-M12-4-D 1000 S-M12-4-D	21.04.05.00353
Network cable	NETZ-KA-M12-DK 5m	21.04.05.00354
Connection cable	ASK S-M12-4-D 1000 RJ-45	21.04.05.00355
Connection cable	ASK S-M12-4-D 5000 RJ-45	21.04.05.00356



WWW.SCHMALZ.COM/10.02.02.06591

Compact-Terminal
SCTSi PNT 4



Art.-Nr.: 10.02.02.06591



Ordering Data Spare Parts 10.02.02.06591

Typ		Item number
Silencer insert (round)	SD-EINS 15x16.5 SD	10.02.02.04141
Sieve, round	SIEB 11x2 X-5 0.415/0.22	10.02.02.04404
Set of parts subject to wear ejector	VST SCPS-einstuf-SD	10.02.02.04737



WWW.SCHMALZ.COM/10.02.02.06591