

Compact ejector

# SCP 10 NC AS



Art.-Nr.: 10.02.02.00602



SCP 10 NC AS

Compact ejector SCP is delivered as a ready to connect product (without connection cable).


Available spare parts: silencer box, filter element

Available accessories: connection cable, connection plug

## Technical data

| Attribute                                 | Value                |
|-------------------------------------------|----------------------|
| Nozzle diameter                           | 1.0 mm               |
| Air consumption suction                   | 53.0 l/min           |
| Suction rate (max.)                       | 37.0 l/min           |
| Pressure range (operating pressure) [bar] | bar                  |
| Shape compact ejectors                    | With blow-off system |
| Control valve                             | Normally closed      |

## Design data



| Attribute           | Value     |
|---------------------|-----------|
| Length L2           | 7.00 mm   |
| Length L            | 71.50 mm  |
| Width B             | 20.20 mm  |
| Height H1           | 101.50 mm |
| Height H2           | 36.50 mm  |
| Height H            | 42.20 mm  |
| Internal diameter d | 4.50 mm   |
| Thread G1           | G1/8"-F   |
| Thread G2           | G1/8"-F   |
| Height H3           | 15.00 mm  |
| Hole spacing Y1     | 12.0 mm   |
| Hole spacing X1     | 41.5 mm   |
| Hole spacing X2     | 58.5 mm   |

Design data SCP 10 NC AS



[WWW.SCHMALZ.COM/10.02.02.00602](http://WWW.SCHMALZ.COM/10.02.02.00602)

Compact ejector  
**SCP 10 NC AS**



Art.-Nr.: 10.02.02.00602



### Technical data

| Attribute            | Value           |
|----------------------|-----------------|
| Nozzle diameter      | 1.0 mm          |
| Degree of evacuation | 85.0 %          |
| Suction rate (max.)  | 1.306 cfm       |
| Product family       | SCP             |
| Control valve        | Normally closed |

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.02.02.00602](http://www.schmalz.com/10.02.02.00602)



### Ordering Data Accessories 10.02.02.00602

| Typ              |                       | Item number    |
|------------------|-----------------------|----------------|
| Connection cable | ASK B-MIC10 3000 K-2P | 21.04.06.00086 |



### Ordering Data Spare Parts 10.02.02.00602

| Typ                    |                            | Item number    |
|------------------------|----------------------------|----------------|
| Filter insert (round)  | FILT-EINS 13x33 PE-POR SCP | 10.02.02.00655 |
| Silencer (cube-shaped) | SD 28x19x31.5 SCP10/15     | 10.02.02.00653 |



[WWW.SCHMALZ.COM/10.02.02.00602](http://WWW.SCHMALZ.COM/10.02.02.00602)