

Art.-Nr.: 10.03.01.00337



EVE-TR 80 AC3 IE3-TYP1 F

The vacuum pump EVE-TR comes ready to connect.


Available spare parts: Filter insert, wearing part set
Available accessories: Vacuum limiter valve

Technical data

Attribute	Value
Rated power at 50 Hz	2.20 kW
Rated power at 60 Hz	2.60 kW
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Weight	78.000 kg
Suction rate (50 Hz)	67.000 m ³ /h
Suction rate (60 Hz)	78.500 m ³ /h
Sound pressure level at 50 Hz	72.0 dB(A)
Version	IE3:EU/CN/IND
Vacuum (50 Hz)	-900 mbar

Design data

Attribute	Value
Length L1	740.00 mm
Length L2	96.00 mm
Length L	704.00 mm
Width B2	46.00 mm
Width B	353.00 mm
Height H1	415.00 mm
Height H2	75.00 mm
Height H	328.00 mm
Internal diameter d	12.00 mm
Thread G2	G1-1/4"-F



Design data EVE-TR 80 AC3 IE3-TYP1 F




Art.-Nr.: 10.03.01.00337

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	2.20 kW
Rated power at 60 Hz	2.60 kW
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Weight	78.000 kg
Suction rate (50 Hz)	67.000 m ³ /h
Suction rate (60 Hz)	78.500 m ³ /h
Sound pressure level at 50 Hz	72.0 dB(A)
Version	IE3:EU/CN/IND
Product family	EVE-TR
Supply voltage	AC3
Current type	Three phase A.C.

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

Typ	0	200	400	600	800	900
EVE-TR 80 50 Hz	68	52	37	23	8.8	2.5
EVE-TR 80 60 Hz	79	61	43.5	28.5	12	3.5



Art.-Nr.: 10.03.01.00337

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00337**Ordering Data Accessories 10.03.01.00337**

Typ		Item number
Vacuum limiter valve	VBV -950...0 G1-1/4-AG EVE 60-140	10.03.01.00153
Silencer box	SBB-EVE-ST-VZ	10.04.04.00368

**Ordering Data Spare Parts 10.03.01.00337**

Typ		Item number
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN	10.07.01.00018

**Ordering Data Wear Parts 10.03.01.00337**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR60/TR80	22.09.01.00031