

Mini compact ejector

SCPMc 12 S04 NO M8-6 NPN DET



Art.-Nr.: 10.02.02.06472



Technical data

Construction vacuum switch	NPN switching
Electrical connection	Male connect M8, 6 pole
Protection type IP	IP 40
Max. vacuum	920 mbar
Sound pressure level free	76.0 dB(A)
Air consumption suction	51.0 l/min
Suction rate (max.)	30.0 l/min
Connection	Hose D6(1)-D6(2)
Pressure range (operating pressure) [bar]	3.5 ... 6.0 bar
Control valve	Normally open

SCPMc 12 S04 NO M8-6 NPN DET

Compact ejector SCPM is delivered as a ready-to-connect product (without connection cable).

Available spare parts: silencer, filter element


Available accessories: connection cable, connection plug



WWW.SCHMALZ.COM/10.02.02.06472

1

Art.-Nr.: 10.02.02.06472

**Design data**

Length L1	120.50 mm
Length L2	11.40 mm
Length L	76.50 mm
Width B1	12.50 mm
Width B	12.00 mm
Height H1	73.90 mm
Height H2	24.95 mm
Height H	65.30 mm
Outside diameter D	10.50 mm
Internal diameter d1	6.2 mm
d2	6.2 mm
Length L3	20.50 mm
Height H3	7.50 mm
Height H4	30.00 mm
Hole spacing X1	36.0 mm
Hole size d4	4.3 mm
Height H5	7.50 mm
Height H6	17.50 mm
Thread G3	M8x1-M

Design data SCPMc 12 S04 NO M8-6 NPN DET

**Technical data**


Construction vacuum switch	NPN switching
Control valve	NO
Recommended hose internal diameter compressed air	4.0 mm
Recommended hose internal diameter vacuum	4.0 mm
Degree of evacuation	92.0 %
Max. vacuum	920 mbar
Weight	84.00 g
Max. air consumption blow-off	10.0 l/min
Air consumption suction	51.0 l/min
Suction rate (max.)	30.0 l/min
Optimal operating pressure	4.50 bar
Pressure range (operating pressure) [bar]	3.5 ... 6.0 bar
Operating temperature	0 ... 50 °C
Product family	SCPMc
Electrical connection	M8-6



Art.-Nr.: 10.02.02.06472



Performance data



Achievable vacuum at various operating pressures



Achievable vacuum at various operating pressures

Typ	2	2.5	3.0	3.5	4	4.5	5	5.5	6
SCPM 03/05/07	416	512	711	866	880	875	860	850	845
SCPM 10	350	416	512	725	866	880	870	860	850
SCPM 12	330	460	610	740	850	922	930	927	925



Ordering Data Accessories 10.02.02.06472

Typ		Item number
Connection cable	ASK WB-M8-6 2000 K-6P	21.04.05.00488
Connection cable	ASK WB-M8-6 2000 S-M12-5	21.04.05.00489
Connection cable	ASK B-M8-6 5000 K-6P	21.04.05.00255
Distributor	ASV SCPMi B-M8-6 2xS-M12-4	10.02.02.05602
Silencer (round)	SD 10.5x31.7 SCPM	10.02.02.05807
Mounting set	SET SCPM MOUNT1	10.02.02.05805
Mounting bracket	BEF-WIN 15x50x36.1 1.5 SCPM	10.02.02.05824
Plug union, straight	STV-GE M5-AG 4	10.08.02.00468
Plug union, straight	STV-GE M7-AG 6	10.08.02.00469
Thread adapter (inst)	ADP-G M7-IG 10.8x7.9 SCPMi/c/b	10.02.02.05522
Thread adapter (inst)	ADP-G M5-IG 10.5x8.6 SCPMi/c/b	10.02.02.05643



Mini compact ejector

SCPMc 12 S04 NO M8-6 NPN DET



Art.-Nr.: 10.02.02.06472



Ordering Data Spare Parts 10.02.02.06472

Typ		Item number
Set of wearing parts ejector	VST SCPMi/c/b	10.02.02.06536



WWW.SCHMALZ.COM/10.02.02.06472