


Art.-Nr.: 10.03.01.00387



EVE-TR 140 AC3 IE3-TYP3 VBV

The vacuum pump EVE-TR comes ready to connect.


Available spare parts: Filter insert, wearing part set
Available accessories: Vacuum limiter valve

Technical data

Attribute	Value
Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.50 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	118.000 kg
Suction rate (50 Hz)	129.000 m ³ /h
Suction rate (60 Hz)	154.000 m ³ /h
Sound pressure level at 50 Hz	76.0 dB(A)
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	-900 mbar
Voltage 60 Hz	S069
Approval	UL/CSA
Current type	Three phase A.C.
with	Vacuum-limiter valve

Design data

Attribute	Value
Length L2	140.00 mm
Length L	862.00 mm
Width B2	107.50 mm
Width B	470.00 mm
Height H	336.00 mm
Internal diameter d	12.00 mm
Hole spacing Y1	245.0 mm
Hole spacing Y2	122.5 mm
Hole spacing X1	398.0 mm
Thread G3	G1-1/2"-F
Thread G5	M8-F



Design data EVE-TR 140 AC3 IE3-TYP3 VBV




Art.-Nr.: 10.03.01.00387


**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.50 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	118.000 kg
Suction rate (50 Hz)	129.000 m ³ /h
Suction rate (60 Hz)	154.000 m ³ /h
Sound pressure level at 50 Hz	76.0 dB(A)
Version	IE3:JPN/KOR/BRA
Product family	EVE-TR
Supply voltage	AC3
Current type	Three phase A.C.

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Performance data**

Suction rate at various degrees of evacuation



Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

Typ	0	200	400	600	800
EVE-TR 140 60 Hz	152	121	89	51	14



Art.-Nr.: 10.03.01.00387

Typ	0	200	400	600	800	900
EVE-TR 140 50 Hz	130	100	70	40	12.5	1

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00387**Ordering Data Accessories 10.03.01.00387**

Typ		Item number
Accessories	ZUB EVE-TR 10-140, Presse mit Fett	10.03.01.00540
Vacuum reservoir	VOL 200	10.03.03.00128

**Ordering Data Spare Parts 10.03.01.00387**

Typ		Item number
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN	10.07.01.00018
Set of parts subject to wear pump	VST EVE-TR-140	22.09.01.00035