

Art.-Nr.: 10.04.01.00073




SB 325 265 3 IE3-TYP3

The vacuum blower SB is delivered as a ready-to-connect product.

Available accessories: silencer box, dust filter

Technical data

Attribute	Value
Rated power at 50 Hz	3.00 kW
Rated power at 60 Hz	3.60 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	42.500 kg
Suction rate (50 Hz)	325.000 m ³ /h
Suction rate (60 Hz)	390.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	265 mbar



Design data SB 325 265 3 IE3-TYP3

Design data


Attribute	Value
Length L	494.00 mm
Width B1	439.00 mm
Width B	370.00 mm
Height H	426.00 mm
Outside diameter D2	60.0 mm
Internal diameter d	10.20 mm
Thread G1	G2"-F
Hole spacing Y1	290.0 mm
Hole spacing X1	290.0 mm

Art.-Nr.: 10.04.01.00073

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	3.00 kW
Rated power at 60 Hz	3.60 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	42.500 kg
Suction rate (50 Hz)	325.000 m ³ /h
Suction rate (60 Hz)	390.000 m ³ /h
Sound pressure level at 50 Hz	70.1 dB(A)
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	265 mbar
Vacuum (60 Hz)	245 mbar
Product family	SB
Version design	IE3-TYP3
Sound pressure level at 60 Hz	71.0 dB(A)

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

	0	100	150	200	250
SB-325-265 (50 Hz)	325	225	180	140	105
SB-390-245 (50 Hz)	390	345	300	260	220



Vacuum blower

SB 325 265 3 IE3-TYP3



Art.-Nr.: 10.04.01.00073



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00073



Ordering Data Accessories 10.04.01.00073

Typ		Item number
Silencer box	SBB-230V-AC-ST/ABS-LUE SB	10.04.04.00235
Silencer box	SBB-24V-DC-ST/ABS-LUE SB	10.04.04.00320
Dust filter	STF 60 P 8.0	10.07.01.00384
Silencer kit	SD SB FITTING SD	10.04.04.00363
Silencer (round)	SD G2-AG 115x380 SB	10.04.04.00374
Rubber buffer (round)	GUMM-PUF 101x55 M6-AG SB 3	10.04.04.00385



WWW.SCHMALZ.COM/10.04.01.00073