

Art.-Nr.: 10.04.01.00079



SB 510 200 4 IE3-TYP3

The vacuum blower SB is delivered as a ready-to-connect product.


Available assesories: silencer box, dust filter

Technical data

Attribute	Value
Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.80 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	61.500 kg
Suction rate (50 Hz)	510.000 m ³ /h
Suction rate (60 Hz)	610.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	200 mbar

Design data

Attribute	Value
Length L	496.00 mm
Width B1	496.00 mm
Width B	474.00 mm
Height H	523.00 mm
Outside diameter D2	76.0 mm
Internal diameter d	12.00 mm
Thread G1	G2"-F
Hole spacing Y1	310.0 mm
Hole spacing X1	310.0 mm




Design data SB 510 200 4 IE3-TYP3

Art.-Nr.: 10.04.01.00079

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.80 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	61.500 kg
Suction rate (50 Hz)	510.000 m ³ /h
Suction rate (60 Hz)	610.000 m ³ /h
Sound pressure level at 50 Hz	75.5 dB(A)
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	200 mbar
Vacuum (60 Hz)	175 mbar
Product family	SB
Version design	IE3-TYP3
Sound pressure level at 60 Hz	76.7 dB(A)

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

	0	100	150	175
SB-510-200 (50 Hz)	510	384	327	300
SB-610-175 (60 Hz)	610	510	480	468



Art.-Nr.: 10.04.01.00079

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00079**Ordering Data Accessories 10.04.01.00079**

Typ		Item number
Silencer box	SBB-230V-AC-ST/ABS-LUE SB	10.04.04.00237
Silencer box	SBB-24V-DC-ST/ABS-LUE SB	10.04.04.00322
Dust filter	STF 75 P 12.0 SSD	10.07.01.00399
Filter insert (round)	FILT-EINS 194x401 PAP STF-Picl-12	10.07.01.00361
Silencer kit	SD SB FITTING SD	10.04.04.00363
Silencer (round)	SD G2-AG 115x380 SB	10.04.04.00374
Rubber buffer (round)	GUMM-PUF 101x55 M6-AG SB 3	10.04.04.00385

**Ordering Data Spare Parts 10.04.01.00079**

Typ		Item number
Conversion kit	UMR-SET SB Ø76/60	10.04.01.00138