


Art.-Nr.: 10.03.01.00851



EVE-TR 4 AC3 F

The vacuum pump EVE-TR comes ready to connect.


Available spare parts: Filter insert, wearing part set
Available accessories: Vacuum limiter valve

Technical data

| | |
|-------------------------------|-----------------------------|
| Rated power at 50 Hz | 0.18 kW |
| Rated power at 60 Hz | 0.21 kW |
| Voltage at 50 Hz | 175 - 260 / 300 - 450 V AC3 |
| Voltage at 60 Hz | 202-300/350-520V AC3 |
| Weight | 7.850 kg |
| Suction rate (50 Hz) | 4.100 m ³ /h |
| Suction rate (60 Hz) | 4.700 m ³ /h |
| Sound pressure level at 50 Hz | 59.0 dB(A) |
| Vacuum (50 Hz) | 850 mbar |
| Voltage 60 Hz | 202-300 |
| Approval | UL |
| Current type | Three phase A.C. |
| with | Filter |

Design data

| | |
|---------------------|-----------|
| Length L1 | 266.50 mm |
| Length L2 | 72.00 mm |
| Length L | 221.50 mm |
| Width B2 | 11.50 mm |
| Width B | 155.00 mm |
| Height H1 | 162.00 mm |
| Height H | 148.00 mm |
| Internal diameter d | 7.00 mm |
| Thread G2 | G1/4"-F |
| Hole spacing Y1 | 100.0 mm |
| Hole spacing X1 | 80.0 mm |
| Thread G3 | G1/4"-F |



Design data EVE-TR 4 AC3 F

Art.-Nr.: 10.03.01.00851

**Technical data**

| | |
|-------------------------------|-----------------------------|
| Protection type IP | IP 54 |
| Rated power at 50 Hz | 0.18 kW |
| Rated power at 60 Hz | 0.21 kW |
| Voltage at 50 Hz | 175 - 260 / 300 - 450 V AC3 |
| Voltage at 60 Hz | 202-300/350-520V AC3 |
| Weight | 7.850 kg |
| Suction rate (50 Hz) | 4.100 m ³ /h |
| Suction rate (60 Hz) | 4.700 m ³ /h |
| Sound pressure level at 50 Hz | 59.0 dB(A) |
| Product family | EVE-TR |
| Supply voltage | AC3 |
| Current type | Three phase A.C. |

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Ordering Data Accessories 10.03.01.00851**

| Typ | | Item number |
|----------------------|------------------------------|----------------|
| Vacuum limiter valve | VBV -850...0 G3/8-AG EVE 4-8 | 10.03.01.00107 |
| Vacuum reservoir | VOL 5 | 10.03.03.00108 |

**Ordering Data Spare Parts 10.03.01.00851**

| Typ | | Item number |
|-----------------------------------|------------------------------------|----------------|
| Filter insert (round) | FILT-EINS 15 27x23 A2 VF-1/4-Draht | 10.07.01.00013 |
| Set of parts subject to wear pump | VST EVE-TR-4 | 10.03.01.00108 |

