

Vacuum blower

# SBV-248-520-FU



Art.-Nr.: 11.02.05.10191



SBV-248-520-FU

## Technical data

| Attribute                     | Value                     |
|-------------------------------|---------------------------|
| Rated power at 50 Hz          | 4.00 kW                   |
| Rated power at 60 Hz          | 4.00 kW                   |
| Voltage at 50 Hz              | 400 - 480 V AC3           |
| Voltage at 60 Hz              | 400 - 480 V AC3           |
| Weight                        | 51.000 kg                 |
| Suction rate (50 Hz)          | 248.000 m <sup>3</sup> /h |
| Suction rate (60 Hz)          | 248.000 m <sup>3</sup> /h |
| Sound pressure level at 50 Hz | 70.0 dB(A)                |
| Vacuum (50 Hz)                | -520 mbar                 |
| Approval                      | UL/CSA                    |

## Design data

| Attribute           | Value     |
|---------------------|-----------|
| Length L            | 493.00 mm |
| Width B             | 370.00 mm |
| Height H            | 456.00 mm |
| Internal diameter d | 12.00 mm  |
| Hole spacing X1     | 290.0 mm  |

Design data SBV-248-520-FU



## Technical data

| Attribute                     | Value                     |
|-------------------------------|---------------------------|
| Protection type IP            | IP 55                     |
| Rated power at 50 Hz          | 4.00 kW                   |
| Rated power at 60 Hz          | 4.00 kW                   |
| Voltage at 50 Hz              | 400 - 480 V AC3           |
| Voltage at 60 Hz              | 400 - 480 V AC3           |
| Weight                        | 51.000 kg                 |
| Suction rate (50 Hz)          | 248.000 m <sup>3</sup> /h |
| Suction rate (60 Hz)          | 248.000 m <sup>3</sup> /h |
| Sound pressure level at 50 Hz | 70.0 dB(A)                |
| Rated power                   | 4.00 W                    |



Vacuum blower

## SBV-248-520-FU



Art.-Nr.: 11.02.05.10191



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/11.02.05.10191](http://www.schmalz.com/11.02.05.10191)



### Ordering Data Accessories 11.02.05.10191

| Typ               |                             | Item number    |
|-------------------|-----------------------------|----------------|
| Frequency changer | FREQU-UM 50/60 400-480AC3 4 | 22.07.01.00206 |



[WWW.SCHMALZ.COM/11.02.05.10191](http://WWW.SCHMALZ.COM/11.02.05.10191)