

Flat suction cup (round)

PFG 6 FPM-65 N004


Art.-Nr.: 10.01.01.00068



PFG 6 FPM-65 N004

Technical data

Attribute	Value
Suction cup material	Fluorine rubber FPM
Material hardness [Shore A]	65.0 Shore A
Size	6.00
Material property	non-marking



Design data

Attribute	Value
Height H2	2.00 mm
Height H	6.50 mm
Head diameter Dk	7.7 mm
Internal diameter d1	6.0 mm
Internal diameter d	4.00 mm
Spring stroke Z	1.0 mm
Diameter Ds	6.0 mm
Height H3	4.00 mm
Diameter Dmax(S)	6.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data PFG 6 FPM-65 N004



WWW.SCHMALZ.COM/10.01.01.00068

Art.-Nr.: 10.01.01.00068

**Technical data**

Attribute	Value
Nipple family	N 004
Suction cup material	Fluorine rubber FPM
Material hardness [Shore A]	65.0 Shore A
Workpiece radius min. (convex)	7.5 mm
Suction force (-600mbar)	1.20 N
Weight	0.30 g
Volume	0.100 cm ³
Size	6.00
Product family	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00068

**Ordering Data Accessories 10.01.01.00068**

Typ		Item number
Suction cup connection nipple	SA-NIP N004 G1/8-AG DN200	10.01.01.03528
Suction cup connection nipple	SA-NIP N004 G1/8-IG DN200	10.01.01.03520
Suction cup connection nipple	SA-NIP N004 M5-AG DN200	10.01.01.03526
Suction cup connection nipple	SA-NIP N004 M5-IG DN200	10.01.01.03518

