

Flat suction cup (round)

PFYN 50 SI-55 G1/8-IG



Art.-Nr.: 10.01.01.00105



Technical data


Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	50.00
Vacuum connection	G 1/8"-F
Nipple material	Aluminum

PFYN 50 SI-55 G1/8-IG

Suction cup PFYN (elastomer part + connection nipple) is delivered unassembled (diameters of 120 mm and more are assembled). The delivery consists of:

- Suction cup of type PFG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup PFG, connection nipple SA-NIP



Design data

Height H	31.00 mm
Nominal diameter dn	3.50 mm
Thread G1	G 1/8"-F
Thread length LG1	9.0 mm
Key width SW1	14.0 mm
Spring stroke Z	4.0 mm
Diameter Ds	50.0 mm
Diameter Dmax(S)	53.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data PFYN 50 SI-55 G1/8-IG



WWW.SCHMALZ.COM/10.01.01.00105

1

Art.-Nr.: 10.01.01.00105

**Technical data**

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	75.0 mm
Suction force (-600mbar)	91.00 N
Weight	17.30 g
Volume	7.000 cm ³
Size	50.00
Number of folds	0.0
Product family	PFYN

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.01.00105**

Typ		Item number
Suction cup cover	SU 50	10.01.01.12837

**Ordering Data Spare Parts 10.01.01.00105**

Typ		Item number
Suction cup connection nipple	SA-NIP N008 G1/8-IG DN350	10.01.01.03524

**Ordering Data Wear Parts 10.01.01.00105**

Typ		Item number
Flat suction cup (round)	PFG 50 SI-55 N008	10.01.01.00037

