

Art.-Nr.: 10.01.01.00132



Technical data


Suction cup material	Fluorine rubber FPM
Material hardness [Shore A]	65.0 Shore A
Size	40.00
Vacuum connection	G 1/8"-F
Nipple material	Aluminum
Material property	non-marking

PFYN 40 FPM-65 G1/8-IG

Suction cup PFYN (elastomer part + connection nipple) is delivered unassembled (diameters of 120 mm and more are assembled). The delivery consists of:

- Suction cup of type PFG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup PFG, connection nipple SA-NIP



Design data

Height H	30.00 mm
Nominal diameter dn	3.50 mm
Thread G1	G 1/8"-F
Thread length LG1	9.0 mm
Key width SW1	14.0 mm
Spring stroke Z	3.5 mm
Diameter Ds	40.0 mm
Diameter Dmax(S)	43.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data PFYN 40 FPM-65 G1/8-IG



Art.-Nr.: 10.01.01.00132

**Technical data**

Suction cup material	Fluorine rubber FPM
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	50.0 mm
Suction force (-600mbar)	57.70 N
Weight	16.20 g
Volume	3.800 cm ³
Size	40.00
Number of folds	0.0
Product family	PFYN

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.01.00132**

Typ		Item number
Suction cup cover	SU 40	10.01.01.12856

**Ordering Data Spare Parts 10.01.01.00132**

Typ		Item number
Suction cup connection nipple	SA-NIP N007 G1/8-IG DN350	10.01.01.03523

**Ordering Data Wear Parts 10.01.01.00132**

Typ		Item number
Flat suction cup (round)	PFG 40 FPM-65 N007	10.01.01.00076

