

Flat suction cup (round)

## PFYN 6 SI-55 M5-AG



Art.-Nr.: 10.01.01.00152



### Technical data


Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	6.00
Vacuum connection	M5-M
Nipple material	Aluminum

PFYN 6 SI-55 M5-AG

Suction cup PFYN (elastomer part + connection nipple) is delivered unassembled (diameters of 120 mm and more are assembled). The delivery consists of:

- Suction cup of type PFG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup PFG, connection nipple SA-NIP



### Design data

Height H	11.50 mm
Nominal diameter dn	2.00 mm
Thread G1	M5-M
Thread length LG1	4.5 mm
Key width SW1	8.0 mm
Spring stroke Z	1.0 mm
Diameter Ds	6.0 mm
Diameter Dmax(S)	6.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data PFYN 6 SI-55 M5-AG



[WWW.SCHMALZ.COM/10.01.01.00152](http://WWW.SCHMALZ.COM/10.01.01.00152)

1

Flat suction cup (round)

## PFYN 6 SI-55 M5-AG



Art.-Nr.: 10.01.01.00152



### Technical data

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	7.5 mm
Suction force (-600mbar)	1.20 N
Weight	1.10 g
Volume	0.008 cm <sup>3</sup>
Size	6.00
Number of folds	0.0
Product family	PFYN

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



### Ordering Data Spare Parts 10.01.01.00152

Typ	Item number
Suction cup connection nipple	SA-NIP N004 M5-AG DN200 10.01.01.03526



### Ordering Data Wear Parts 10.01.01.00152

Typ	Item number
Flat suction cup (round)	PFG 6 SI-55 N004 10.01.01.00028



[WWW.SCHMALZ.COM/10.01.01.00152](http://WWW.SCHMALZ.COM/10.01.01.00152)