




PFG 120 NBR-55 N010

Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	55.0 Shore A
размер	120.00



Конструктивные данные

Attribute	Value
Высота H	23.50 mm
Диаметр головки Dk	89.5 mm
Внутренний диаметр d	7.00 mm
Ход пружины Z	6.0 mm
Диаметр Ds	120.0 mm
Диаметр Dmax(S)	124.0 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные PFG 120 NBR-55 N010

Art.-Nr.: 10.01.01.00331



Технические данные

Attribute	Value
Семейство ниппелей	N 010
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	55.0 Shore A
Радиус заготовки мин. (выпуклый)	300.0 mm
Всасывающая сила (-600 мбар)	540.00 N
Вес	233.5 g
Объем	75.164 cm ³
размер	120.00
Семейство продуктов	PFG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00331

Заказать аксессуары для данных **10.01.01.00331**

Тип	Artikelnummer
Плоская присоска (круглая) PFG 120 FPM-65 N010	10.01.01.00389

