

Düz vantuz (yuvarlak)

SGA 16 SI-55 N029




Art.-Nr.: 10.01.01.00452



SGA 16 SI-55 N029

Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
Boyut	16.00



Tasarım verileri SGA 16 SI-55 N029

Tasarım verileri

Attribute	Value
Yükseklik H2	2.00 mm
Yükseklik H	12.00 mm
Kafa çapı Dk	16.0 mm
İç çap d1	12.0 mm
İç çap d	9.00 mm
Yay stroku Z	2.0 mm
Çap Ds	15.0 mm
Yükseklik H3	4.00 mm
Çap Dmax(S)	17.5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00452

Düz vantuz (yuvarlak)

SGA 16 SI-55 N029



Art.-Nr.: 10.01.01.00452



Teknik veriler

Attribute	Value
Vantuz malzemesi	Silikon SI
Malzeme sertliği [Shore A]	55.0 Shore A
İş parçası yarıçapı dak (dışbükey)	15.0 mm
Emme kuvveti (-600mbar)	6.90 N
Ağırlık	1.1 g
Cilt	0.607 cm ³
Boyut	16.00
Körük Sayısı	0.0
Ürün ailesi	SGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00452



Veri aksesuarları sipariş edin 10.01.01.00452

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N029 G1/8-AG DN350
Vantuz bağlantı nipel	SA-NIP N029 G1/8-IG DN350



WWW.SCHMALZ.COM/10.01.01.00452