




SPL-HT 90 FPM-F-65

Technical data

Attribute	Value
Suction cup material	Fluorine rubber FPM-F
Material hardness [Shore A]	65.0 Shore A
Size	90.00
Working temperature max.	350.0 °C



Design data SPL-HT 90 FPM-F-65

Design data

Attribute	Value
Height H2	4.00 mm
Height H	36.00 mm
Head diameter Dk	86.0 mm
Internal diameter d1	78.0 mm
d2	4.0 mm
Internal diameter d	72.00 mm
Spring stroke Z	16.5 mm
Diameter Ds	90.0 mm
Height H3	9.50 mm
Diameter Dmax(S)	98.0 mm

Suction plate (round)

SPL-HT 90 FPM-F-65



Art.-Nr.: 10.01.01.00553



Technical data

Attribute	Value
Suction cup material	Fluorine rubber FPM-F
Workpiece radius min. (convex)	250.0 mm
Suction force (-600mbar)	230.00 N
Weight	79.2 g
Volume	119.000 cm ³
Size	90.00
Working temperature max.	350.0 °C
Product family	SPL-HT

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00553



WWW.SCHMALZ.COM/10.01.01.00553