


Düz vantuz (yuvarlak)

SGA 13 PU-55 N029




Art.-Nr.: 10.01.01.00571



SGA 13 PU-55 N029

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	13,00



Tasarım verileri SGA 13 PU-55 N029

Tasarım verileri

Attribute	Value
Yükseklik H2	1,80 mm
Yükseklik H	11,50 mm
Kafa çapı Dk	14,8 mm
İç çap d1	11,9 mm
İç çap d	8,80 mm
Yay stroku Z	2,0 mm
Çap Ds	12,0 mm
Yükseklik H3	3,60 mm
Çap Dmax(S)	13,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00571

Art.-Nr.: 10.01.01.00571

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	12,5 mm
Emme kuvveti (-600mbar)	4,70 N
Ağırlık	1,30 g
Cilt	0,441 cm ³
Boyut	13,00
Körük Sayısı	0,0
Ürün ailesi	SGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00571

**Sipariş Verisi Aksesuarlar 10.01.01.00571**

Typ	Ürün numarası
Vantuz bağlantı nipeli	SA-NIP N029 G1/8-AG DN350
Vantuz bağlantı nipeli	SA-NIP N029 G1/8-IG DN350

WWW.SCHMALZ.COM/10.01.01.00571