




SPL-HT 90 FPM-F-65

Технические данные

Attribute	Value
Материал присоски	Фторкаучук FPM-F
Твердость материала [Shore A]	65.0 Shore A
размер	90.00
Рабочая температура макс.	350.0 °C



Конструктивные данные SPL-HT 90 FPM-F-65

Конструктивные данные

Attribute	Value
Высота H2	4.00 mm
Высота H	36.00 mm
Диаметр головки Dk	86.0 mm
Внутренний диаметр d1	78.0 mm
d2	4.0 mm
Внутренний диаметр d	72.00 mm
Ход пружины Z	16.5 mm
Диаметр Ds	90.0 mm
Высота H3	9.50 mm
Диаметр Dmax(S)	98.0 mm

Art.-Nr.: 10.01.01.00553



Технические данные

Attribute	Value
Материал присоски	Фторкаучук FPM-F
Радиус заготовки мин. (выпуклый)	250.0 mm
Всасывающая сила (-600 мбар)	230.00 N
Вес	79.2 g
Объем	119.000 cm ³
размер	90.00
Рабочая температура макс.	350.0 °C
Семейство продуктов	SPL-HT

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00553

