

Düz vantuz (yuvarlak)

SGA 9 PU-60 N028


Art.-Nr.: 10.01.01.00569



SGA 9 PU-60 N028

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	9,00



Tasarım verileri SGA 9 PU-60 N028

Tasarım verileri

Attribute	Value
Yükseklik H2	2,00 mm
Yükseklik H	12,00 mm
Kafa çapı Dk	9,0 mm
İç çap d1	7,0 mm
İç çap d	5,00 mm
Yay stroku Z	1,5 mm
Çap Ds	8,0 mm
Yükseklik H3	4,00 mm
Çap Dmax(S)	9,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00569

Düz vantuz (yuvarlak)

SGA 9 PU-60 N028



Art.-Nr.: 10.01.01.00569



Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	60,0 Shore A
İş parçası yarıçapı dak (dışbükey)	10,0 mm
Emme kuvveti (-600mbar)	2,10 N
Ağırlık	0,50 g
Cilt	0,200 cm ³
Boyut	9,00
Körük Sayısı	0,0
Ürün ailesi	SGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00569



Sipariş Verisi Aksesuarlar 10.01.01.00569

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N028 M5-AG DN200 10.01.01.00753
Vantuz bağlantı nipel	SA-NIP N028 M5-IG DN200 10.01.01.00813



WWW.SCHMALZ.COM/10.01.01.00569