

Düz vantuz (yuvarlak)

SGA 7 PU-55 N028


Art.-Nr.: 10.01.01.00570



SGA 7 PU-55 N028

Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55,0 Shore A
Boyut	7,00



Tasarım verileri SGA 7 PU-55 N028

Tasarım verileri

Attribute	Value
Yükseklik H2	2,00 mm
Yükseklik H	12,00 mm
Kafa çapı Dk	9,0 mm
İç çap d1	7,0 mm
İç çap d	5,00 mm
Yay stroku Z	1,0 mm
Çap Ds	7,0 mm
Yükseklik H3	4,00 mm
Çap Dmax(S)	7,5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.00570

Düz vantuz (yuvarlak)

SGA 7 PU-55 N028



Art.-Nr.: 10.01.01.00570



Teknik veriler

Attribute	Value
Vantuz malzemesi	Poliüretan PU
Malzeme sertliği [Shore A]	55,0 Shore A
İş parçası yarıçapı dak (dışbükey)	7,5 mm
Emme kuvveti (-600mbar)	1,60 N
Ağırlık	0,50 g
Cilt	0,186 cm ³
Boyut	7,00
Körük Sayısı	0,0
Ürün ailesi	SGA

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00570



Sipariş Verisi Aksesuarlar 10.01.01.00570

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N028 M5-AG DN200
Vantuz bağlantı nipel	SA-NIP N028 M5-IG DN200



WWW.SCHMALZ.COM/10.01.01.00570