

Suction plate (round)

SPU 210 SI-60 G1/2-IG TV



Art.-Nr.: 10.01.01.01150



Technical data


Suction cup material	Silicone SI
Material hardness [Shore A]	60.0 Shore A
Size	210.00
Connection	G1/2"-F

SPU 210 SI-60 G1/2-IG TV

Suction plate SPU (sealing ring + support plate) is delivered assembled. The assembly consists of:

- Sealing ring of type DR-SPU – elastomer part, available in various diameters
- Aluminum support plate, available with various threads
- Optional product addition: touch valve, steep sealing lip, peeling insert

Available spare parts: sealing ring DR-SPU, touch valve TV



Design data

Length L2	36.50 mm
Height H1	51.00 mm
Height H	25.00 mm
d2	163.0 mm
Internal diameter d	34.00 mm
Thread G1	G1/2"-F
Thread length LG1	13.5 mm
Thread G2	G1/4"-M
Thread length LG2	13.0 mm
Thread length LG3	6.0 mm
Spring stroke Z	5.0 mm
Diameter Ds	210.0 mm
Diameter Dmax(S)	220.0 mm
Thread G3	G1/8"-F

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SPU 210 SI-60 G1/2-IG TV



WWW.SCHMALZ.COM/10.01.01.01150

1

Art.-Nr.: 10.01.01.01150

**Technical data**

Suction cup material	Silicone SI
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	9.0 mm
Workpiece radius min. (convex)	750.0 mm
Suction force (-600mbar)	1,870.00 N
Weight	840.0 g
Volume	192.000 cm ³
Size	210.00
Suction force d2	1,250.00 N
Number of folds	0.0
Product family	SPU

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.01.01150**

Typ		Item number
Suction cup cover	SU 210	10.01.01.12439

**Ordering Data Spare Parts 10.01.01.01150**

Typ		Item number
Touch Valve	TV G1/4-AG 13	10.05.10.00061

**Ordering Data Wear Parts 10.01.01.01150**

Typ		Item number
Sealing ring for SPU suction plate	DR-SPU 210 SI-60	10.01.01.01090

