


Art.-Nr.: 10.01.01.00834



SPL-HT 190 FPM-F-65

Технические данные

Attribute	Value
Материал присоски	Фторкаучук FPM-F
Твердость материала [Shore A]	65.0 Shore A
размер	190.00
Рабочая температура макс.	350.0 °C



Конструктивные данные

Attribute	Value
Высота H	17.00 mm
Внутренний диаметр d	40.00 mm
Ход пружины Z	8.0 mm
Диаметр Ds	190.0 mm
Диаметр Dmax(S)	209.0 mm

Конструктивные данные SPL-HT 190 FPM-F-65



Art.-Nr.: 10.01.01.00834



Технические данные

Attribute	Value
Материал присоски	Фторкаучук FPM-F
Радиус заготовки мин. (выпуклый)	350.0 mm
Всасывающая сила (-600 мбар)	1050.00 N
Вес	256.0 g
размер	190.00
Рабочая температура макс.	350.0 °C
Семейство продуктов	SPL-HT

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.00834

