



PFYN 40 NBR-CO-55 G1/8-AG

Suction cup PFYN (elastomer part + connection nipple) is delivered unassembled (diameters of 120 mm and more are assembled). The delivery consists of:

- Suction cup of type PFG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup PFG, connection nipple SA-NIP


Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55.0 Shore A
Size	40.00
Vacuum connection	G1/8"-M
Nipple material	Aluminum

Design data

Attribute	Value
Height H	19.00 mm
Nominal diameter dn	2.40 mm
Thread G1	G1/8"-M
Thread length LG1	8.0 mm
Key width SW1	14.0 mm
Spring stroke Z	3.5 mm
Diameter Ds	40.0 mm
Diameter Dmax(S)	43.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



Design data PFYN 40 NBR-CO-55 G1/8-AG

Art.-Nr.: 10.01.01.10389

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR-conductive
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	50.0 mm
Suction force (-600mbar)	57.70 N
Weight	12.20 g
Volume	3.800 cm ³
Size	40.00
Number of folds	0.0
Product family	PFYN

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.10389

**Ordering Data Accessories 10.01.01.10389**

Typ	Item number
Suction cup cover	SU 40 10.01.01.12856

**Ordering Data Spare Parts 10.01.01.10389**

Typ	Item number
Suction Cup Connection Nipples	SA-NIP N007 G1/8-AG DN240 10.01.01.03531

**Ordering Data Wear Parts 10.01.01.10389**

Typ	Item number
Flat suction cup (round)	PFG 40 NBR-CO-55 N007 10.01.01.10341

