

Flat suction cup (round)

## SAF 125 NBR-60 G1/4-AG



Art.-Nr.: 10.01.01.10666




### Technical data

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Size	125.00
Connection	G 1/4-AG
Nipple material	Aluminum

SAF 125 NBR-60 G1/4-AG

Suction cup SAF, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



### Design data

Height H	43.00 mm
Nominal diameter dn	6.00 mm
Thread G1	G1/4"-M
Thread length LG1	10.0 mm
Key width SW1	22.0 mm
Spring stroke Z	12.5 mm
Diameter Ds	125.0 mm
Diameter Dmax(S)	135.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SAF 125 NBR-60 G1/4-AG



[WWW.SCHMALZ.COM/10.01.01.10666](http://WWW.SCHMALZ.COM/10.01.01.10666)

1

Art.-Nr.: 10.01.01.10666

**Technical data**

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	9.0 mm
Workpiece radius min. (convex)	165.0 mm
Suction force (-600mbar)	660.00 N
Weight	155.10 g
Lateral force	475.0 N
Lateral force oily surface	400.0 N
Volume	119.000 cm <sup>3</sup>
Size	125.00
Number of folds	0.0
Product family	SAF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.01.10666**

Typ		Item number
Suction cup cover	SU 120	10.01.01.12437

