

Flat suction cup (round)

SAF 40 NBR-45 M10-AG



Art.-Nr.: 10.01.01.11435




Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	45.0 Shore A
Size	40.00
Connection	M10-AG
Nipple material	Steel

SAF 40 NBR-45 M10-AG

Suction cup SAF, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



Design data

Attribute	Value
Height H	22.00 mm
Nominal diameter dn	4.00 mm
Thread G1	M10-M
Thread length LG1	12.0 mm
Key width SW1	17.0 mm
Spring stroke Z	4.0 mm
Diameter Ds	41.0 mm
Diameter Dmax(S)	46.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SAF 40 NBR-45 M10-AG



WWW.SCHMALZ.COM/10.01.01.11435

1

Art.-Nr.: 10.01.01.11435

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	45.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	50.0 mm
Suction force (-600mbar)	69.00 N
Weight	27.50 g
Lateral force	52.0 N
Lateral force oily surface	50.0 N
Volume	5.300 cm ³
Size	40.00
Number of folds	0.0
Product family	SAF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.11435

**Ordering Data Accessories 10.01.01.11435**

Typ		Item number
Suction cup cover	SU 40	10.01.01.12856

